

**Product Texts**

Vectra® MT1300 VF3001 (natural) is a unfilled easy flow LCP grade for extrusion processing.

Vectra® MT1300 VF3001 (natural) is a special grade developed for medical industry applications and complies with:

- Food Contact Substance Notification (FCN) No. 742 of the Food and Drug Administration (FDA) and is listed in the Drug Master File (DMF 8464) and the Device Master File (MAF 315)
- the corresponding EU and national registry regulatory requirements
- biocompatibility in tests corresponding to USP 23 Class VI/ISO 10993
- low residual monomers
- no animal products

Chemical abbreviation according to ISO 1043-1 : LCP

Inherently flame retardant

Flammability at thickness h V-0

Processing/Physical Characteristics	Value	Unit	Test Standard
-------------------------------------	-------	------	---------------

ISO Data			
<sup>[C]</sup> Molding shrinkage, normal	0.7	%	ISO 294-4, 2577

[C]: CAMPUS

Mechanical properties	Value	Unit	Test Standard
-----------------------	-------	------	---------------

ISO Data			
<sup>[C]</sup> Tensile Modulus	7800	MPa	ISO 527
<sup>[C]</sup> Stress at break	148	MPa	ISO 527
<sup>[C]</sup> Strain at break	5.7	%	ISO 527
<sup>[C]</sup> Charpy impact strength, +23°C	267	kJ/m <sup>2</sup>	ISO 179/1eU
<sup>[C]</sup> Charpy impact strength, -30°C	53	kJ/m <sup>2</sup>	ISO 179/1eU
<sup>[C]</sup> Charpy notched impact strength, +23°C	95	kJ/m <sup>2</sup>	ISO 179/1eA

[C]: CAMPUS

Thermal properties	Value	Unit	Test Standard
--------------------	-------	------	---------------

ISO Data			
<sup>[C]</sup> Melting temperature, 10°C/min	280	°C	ISO 11357-1/-3
<sup>[C]</sup> Temp. of deflection under load, 1.80 MPa	187	°C	ISO 75-1/-2
<sup>[C]</sup> Temp. of deflection under load, 8.00 MPa	94	°C	ISO 75-1/-2
<sup>[C]</sup> Vicat softening temperature, B	145	°C	ISO 306
<sup>[C]</sup> Coeff. of linear therm. expansion, parallel	-2.4	E-6/K	ISO 11359-1/-2
<sup>[C]</sup> Coeff. of linear therm. expansion, normal	81	E-6/K	ISO 11359-1/-2
<sup>[C]</sup> Burning Behav. at thickness h	V-0	class	IEC 60695-11-10

[C]: CAMPUS

Electrical properties	Value	Unit	Test Standard
-----------------------	-------	------	---------------

ISO Data			
<sup>[C]</sup> Relative permittivity, 100Hz	3.2	-	IEC 62631-2-1
<sup>[C]</sup> Relative permittivity, 1MHz	3	-	IEC 62631-2-1
<sup>[C]</sup> Dissipation factor, 100Hz	159	E-4	IEC 62631-2-1
<sup>[C]</sup> Dissipation factor, 1MHz	200	E-4	IEC 62631-2-1
<sup>[C]</sup> Volume resistivity	1E13	Ohm*m	IEC 62631-3-1
<sup>[C]</sup> Surface resistivity	1E14	Ohm	IEC 62631-3-2
<sup>[C]</sup> Electric strength	47	kV/mm	IEC 60243-1

[C]: CAMPUS

Other properties	Value	Unit	Test Standard
------------------	-------	------	---------------

<sup>[C]</sup> Humidity absorption	0.03	%	Sim. to ISO 62
------------------------------------	------	---	----------------

[C] Density

**1400**

kg/m<sup>3</sup>

ISO 1183

[C]: CAMPUS

**Characteristics**

**Processing**

Injection Molding, Film Extrusion, Other Extrusion

**Delivery form**

Pellets, Natural Color

**Special Characteristics**

Flame retardant, Sterilizable, Ethylene Oxide (EtO) Sterilization, Steam sterilization, Gamma irradiation sterilization

**Certifications**

Food contact, Food approval BfR, Food approval FDA 21 CFR, Food contact notification (FCN), Medical Grade, Biocompatibility ISO 10993, US Pharmacopeia Class VI Approved, Drug Master File, Device Master File

**Applications**

Medical

**Regional Availability**

North America, Europe

**Other text information**

**Injection molding**

Vectra resins are well known for their excellent thermal and hydrolytic stability. In order to ensure these properties are optimum, the resin should be dried correctly prior to processing. The Vectra MT-grades MT1300, MT1305, MT1310, MT1335, MT1340 and MT1345 should be dried at 150°C for a minimum of 4 hours in a desiccant dryer.

A three-zone screw evenly divided into feed, compression, and metering zones is preferred. A higher percentage of feed flights may be needed for smaller machines: 1/2 feed, 1/4 compression, 1/4 metering.

Vectra LCPs are shear thinning, their melt viscosity decreases quickly as shear rate increases. For parts that are difficult to fill, the molder can increase the injection velocity to improve melt flow.